



EMERGENCY WASH STATION



**Combination Wash
Station with Shower**

**Wall Mount Eye
Wash Station**



LILY SAFETY

United Kingdom, London
Email: enquiry@lilysafety
(+44) 07311009723



EMERGENCY WASH STATION WITH SAFETY SHOWER

In the event of accidental chemical splash, your safety and health depend upon how quickly you can be treated. These systems provide immediate and effective first aid treatment required.

Safety station combines eye wash and shower from a single water outlet. Stay-open ball valves activate within 1 second. 260mm 304 stainless steel shower head delivers water at 120~180L/Min. The Spray pattern is 20" in diameter at 60" above floor. Stainless steel pull rod is easily located and grasped in an emergency. Eye wash is activated by a ½" IPS stainless steel stay-open ball valve with cast aluminum flag handle. 260mm dia. Stainless steel bowl acts like a sink to drain water away. Unit comes with luminous signs for high visibility. Unit meets ANSI Z358.1 standard as primary eye wash and emergency shower. Complete with ANSI compliant identification sign.

Product Specifications

DESCRIPTION: Safety Station, Eyewash and Drench Shower

CODE WITH FOOT PEDAL: EWST01

CODE WITHOUT FOOT PEDAL: EWST02

COLOR FINISH: Silver

CONSTRUCTION: 304 Stainless Steel

MOUNTING: Plumbing Required, Floor Mount

BOWL MATERIAL: 304 Stainless Steel

BOWL COLOR: Silver

INCLUDES: Flip Top Dust Covers

ADA COMPLIANT: No

INLET/OUTLET SIZE: 1-1/4" NPT Female

BOWL DIAMETER: 260mm

EYE/FACE WASH ACTIVATOR: Push Board or Foot Pedal

SHOWER ACTIVATOR: Pull Handle

MEETS ANSI: Z358.1-2014

EYE/FACE WASH SPRAY HEADS: 2

DUST PROOF COVER: 304 Stainless Steel

SHOWER HEAD MATERIAL: 304 Stainless Steel

SHOWER HEAD DIAMETER: 260mm

FLOW RATE -EYEWASH: 12~18L/Min

FLOW RATE-SHOWER: 120~180L/Min

TYPE: All Purpose Station

EYEWASH FLOW RATE: Non-Adjustable

ASSEMBLY: Unassembled

OPTIONAL SPARE PARTS: foot pedal



Wall Mount Eye Wash Station

Eyewashes are used in hazardous work areas of enterprises such as laboratories, pharmaceuticals, chemicals, petrochemicals, electronics, and semiconductors. When chemical or Toxic materials splash on the eyes of the workers, the device quickly minimizes the damage and reduce the harm to the cause to the eyes caused by toxic and harmful substances.

Product Specifications

DESCRIPTION: Wall Mount Eye Wash Station

CODE: EWST03

MATERIALS: 304 Stainless Steel

SPRINKLER: 304 Stainless Steel

INDICATOR: Luminous Aluminum Alloy

ANTI-DUST COVER: 304 Stainless Steel

EYEWASH OPERATION: Hand Operated

WATER PRESSURE: 0.25 to 0.40 Mpa

EYEWASH FLOW: 12 to 18L Per Minute

SPRINKLER SPACING: 101.6mm

INLET: 1/2"

OUTLET: 1 1/4"

WEIGHT: 3.5 KG

